




M 1:1



Mechanical characteristics

interface dimensions acc. to panel piercing
mating life
recommended torque for panel mounting

Components

inner conductor
outer conductor
lock washer
nut
screws
insulator
insulating body

Electrical characteristics

impedance
frequency
working voltage
voltage proof
insulation resistance
contact resistance
inner conductor
outer conductor

Environmental

operating temp.
RoHS compliant

Mechanische Eigenschaften

Steckgesicht nach Montageausschnitt
Steckzyklen
empfohlenes Anzugsmoment für Einbau in Gehäuse

Bauteile

Innenleiter
Außenleiter
Sicherungsscheibe
Mutter
Schrauben
Isolierung
Isolierkörper

Elektrische Eigenschaften

Wellenwiderstand
Frequenz
Betriebsspannung
Prüfspannung
Isolationswiderstand
Durchgangswiderstand
Innenleiter
Außenleiter

Umgebung

Betriebstemperatur
RoHS konform

IEC 61169-8
Z004 / Z034
>500

1 Nm

Materials / Material

copper alloy / Kupferlegierung
zinc alloy / Zinklegierung
steel / Stahl
brass / Messing
steel / Stahl
PP
PBT white /weiß

Finish / Oberfläche

gold plated / vergoldet
nickel plated / vernickelt
nickel plated / vernickelt
nickel plated / vernickelt
black oxide / schwarz
black oxide / schwarz
black oxide / schwarz

50 Ω
0-1 GHz
< 500 kVeff / 50 Hz
1,5 kVeff / 50 Hz
> 500 MΩ

< 20 mΩ
< 5 mΩ

-45°C / +85°C
2011/65/EU

up to 2.5 mm
on request
bis 2.5 mm
auf Anfrage

Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name		Datum/ date	Name/ name	Gewicht/ weight [g]	
				gez./ drawn	21.11.2024	PU		
				gepr./ appr.	21.11.2024	JM	ca./approx.	
				Maßstab/ scale	Benennung/ title			 Telegärtner
				2:1 (1:1)	BNC Jck str Bkhd sd/sd PCB insul A Z50 BNC Jck str Bkhd sd/sd PCB insul A Z50			
-	500000001785	21.11.2024	PU	untol. Maße/ dim. without tolerances according to	Untert./doc. type	Materialnr./ material no.		 Maße/ dimensions: mm
				CUG		100132568		
				Ersatz für/ replaces	PDM Nr./ pdm no.		10017227	
								Original : DIN A4
								Blatt/ sheet 1 von/ of 1