



18Vx2 Brushless Circular Saw 190mm LXT

DHS783ZJU

Models DHS782 and DHS783 are 190mm cordless circular saws powered by 2x 18V LXT batteries.



TECHNICAL SPECIFICATIONS

Max Cut @ 48°	42 mm
Battery Type	Lithium-ion
Body only machine	✓
Voltage	36 (18V x2) v
Blade Diameter	190 mm
Max Cut @ 0°	62.5 mm
Max Cut @ 45°	44.5 mm
Bore (B)	20 / 30 mm
Noise sound pressure	93 dB(A)
Noise sound power	104 dB(A)
Noise K factor	3 dB(A)
No Load Speed	6,000 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	2.5 m/sec ²
Net weight	4.5 - 5.1 kg

USER BENEFITS

- Brushless motor
- Auto-Start Wireless System (AWS) - connects to compatible dust extractors with Bluetooth. The dust extractor automatically runs while the switch is on.
- Electric brake
- Soft start
- LED job light
- Automatic Torque Drive Technology: Automatically changes the cutting speed according to load condition for optimum operation
- Overload warning lamp
- Compatible with guide rail without adaptor
- Positive stop at 45 degree bevel angle
- Improved visibility of blade tip
- High power similar to AC Tool
- Magnesium die-cast base plate

Link to product - makitauk.com



RELATED PRODUCTS

(Recon

STANDARD ACCESSORIES

821552-6

MAKPAC CONNECTOR CASE (TYPE



OTHER