



Intel Core i3 10320 - 3.8 GHz - 4 Kerne - 8 Threads - 8 MB Cache-Speicher - Box

Produktbeschreibung	Intel Core i3 10320 / 3.8 GHz Prozessor - Box
Produkttyp	Prozessor
Prozessortyp	Intel Core i3 10320 (10. Gen.)
Anz. der Kerne	Quad-Core / 8 Threads
Cache-Speicher	8 MB
Integrierte Grafik	Intel UHD Graphics 630
Prozessoranz.	1
Taktfrequenz	3.8 GHz
Max. Turbo-Taktfrequenz	4.6 GHz
Bus-Geschwindigkeit	8 GT/s
Herstellungsprozess	14 nm
Funktionen	Enhanced SpeedStep technology, Hyper-Threading-Technologie, Unterstützung für Execute Disable Bit, Intel Virtualization Technology, Intel 64 Technology, Streaming-SIMD-Erweiterungen 4.1, Streaming-SIMD-Erweiterungen 4.2, Intel Turbo Boost Technology 2.0, Intel AES New Instructions (AES-NI), Thermal Monitoring Technologies, Intel Virtualization Technology for Directed I/O (VT-d), Idle States, Intel VT-x with Extended Page Tables (EPT), Intel Identity Protection Technology, Intel Secure Key, Intel OS Guard, Intel Software Guard Extensions (SGX), Intel Optane Memory Supported, Intel Boot Guard