

Samsung LH43BEDHLGUXEN visualizzatore di messaggi Pannello piatto per segnaletica digitale 109,2 cm (43") Wi-Fi 4K Ultra HD Nero Tizen 16/7

Marchio : Samsung

Codice prodotto: LH43BEDHLGUXEN

Nome del prodotto : LH43BEDHLGUXEN



Samsung LH43BEDHLGUXEN. Design del prodotto: Pannello piatto per segnaletica digitale. Dimensioni diagonale schermo: 109,2 cm (43"), Risoluzione del display: 3840 x 2160 Pixel, Tipologia HD: 4K Ultra HD. Wi-Fi. Ore di servizio (ore/giorni): 16/7. Sistema operativo incluso: Tizen. Colore del prodotto: Nero

Display		Performance	
Display diagonal *	109.2 cm (43")	Web browser	✓
Display resolution *	3840 x 2160 pixels	Power	
HD type *	4K Ultra HD	Power consumption (typical) *	110 W
Touchscreen *	✗	Energy efficiency class (SDR)	G
Native aspect ratio	16:9	Energy efficiency class (HDR)	G
Display diagonal (metric)	107.9 cm	Energy consumption (SDR) per 1000 hours	53 kWh
High Dynamic Range (HDR) supported	✓	Energy consumption (HDR) per 1000 hours	104 kWh
High Dynamic Range (HDR) technology	Filmmaker Mode, High Dynamic Range 10+ (HDR10 Plus)	Energy efficiency scale	A to G
Ports & interfaces		Computer system	
HDMI ports quantity *	3	Operating system installed	Tizen
USB port *	✓	Weight & dimensions	
USB ports quantity	1	Display width	967.5 mm
Ethernet LAN *	✓	Display depth	59.7 mm
Ethernet LAN (RJ-45) ports	1	Display height	561.4 mm
Wi-Fi *	✓	Display weight	7.1 kg
Wi-Fi standards	Wi-Fi 5 (802.11ac)	Packaging data	
Audio Return Channel (ARC)	✓	Package width	1081 mm
Audio		Package depth	147 mm
Built-in speaker(s) *	✓	Package height	665 mm
RMS rated power	20 W	Package weight	10.5 kg
Audio output channels	2.0 channels	Brand-specific features	
Enhanced Audio Return Channel (eARC)	✓	Samsung technologies (AV/TV)	Media Home, Q-Symphony
Design		Other features	
Product design *	Digital signage flat panel	Bluetooth	✓
Product colour *	Black	Bluetooth version	5.2
Screen shape	Flat	Common interface (CI)	✓
VESA mounting *	✓	Common interface Plus (CI+)	✓
Bezel type	3 Bezel-less	RF ports quantity	1
Performance		Package type	Box
Purpose *	Commercial	Tuner type	Analog & digital
Digital signal format system	DVB-C, DVB-S2, DVB-T2	Common interface Plus (CI+) version	1.4
Operating hours (hours/days)	16/7		



8806095641041

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 09-MAR-2025. Prints or copies of Information are only valid on the printed Publication date