



Lenovo Tab Plus Mediatek 128 GB 29,2 cm (11.5") 8 GB Wi-Fi 5 (802.11ac) Android 14 Grigio

Marchio : Lenovo **Famiglia del prodotto:** Tab **Codice prodotto:** ZADX0091SE
Nome del prodotto : Plus

- MediaTek Helio G99 (8C, 2x A76 @2.2GHz + 6x A55 @2.0GHz)
 - 11.5" 2K (2000x1200) 400nits 72% NTSC 90Hz Touch
 - 8GB LPDDR4x
 - 128GB UFS 2.2
 - Arm Mali-G57 MC2 GPU
 - Android 14 or Later
- MediaTek Helio G99 (8C, 2x A76 @2.2GHz + 6x A55 @2.0GHz), 8GB LPDDR4x, 128GB UFS 2.2, 11.5" 2K (2000x1200) 400nits 72% NTSC 90Hz Touch, Arm Mali-G57 MC2 GPU, Wi-Fi 5 802.11ac 1x1 + BT5.2, Front 8.0MP / Rear 8.0MP, Android 14 or Later



Lenovo Tab Plus Mediatek 128 GB 29,2 cm (11.5") 8 GB Wi-Fi 5 (802.11ac) Android 14 Grigio:

Gioia a ogni battito

- Immergiti nella tua oasi audio personale con otto altoparlanti Dolby Atmos.
- Goditi la musica in streaming wireless ovunque e in qualsiasi momento con la connettività Bluetooth®.
- Immagini vibranti che prendono vita sul display 2K da 29,21 cm (11,5").
- Intrattenimento senza interruzioni per tutto il giorno con una ricarica rapida di 90 minuti.
- Trasforma il tablet in una cornice per immagini con la modalità standby durante la ricarica.

Display		Network	
Display diagonal *	29.2 cm (11.5")	SIM card type	✗
Display resolution *	2000 x 1200 pixels	Ports & interfaces	
LED backlight	✓	USB 2.0 Type-C ports quantity	1
Display technology	LED	Headphone connectivity	3.5 mm
Panel type	IPS	Combo headphone/mic port	✓
Display brightness	400 cd/m²	Phone features	
HD type	2K	Voice call	✗
Native aspect ratio	5:3	Design	
Processor		Colour name	Luna Grey
Processor manufacturer *	MediaTek	Device type *	Mobile tablet
Processor family *	Mediatek	Housing material	Metal, Plastic
Processor model *	Helio G99	Form factor *	Slate
Processor cores	8	Product colour *	Grey
Processor boost frequency	2.2 GHz	International Protection (IP) code	IP52
Performance cores	2	Performance	
Efficient cores	6	Assisted GPS (A-GPS) *	✗
Memory		GLONASS	✓
Internal memory *	8 GB	GPS (satellite)	✓
Internal memory type	LPDDR4x-SDRAM	Galileo	✓
Maximum internal memory	8 GB	Accelerometer	✓
Storage		Ambient light sensor	✓
Internal storage capacity *	128 GB	Gyroscope	✓
Card reader integrated *	✓	Position location *	✓
Compatible memory cards	MicroSD (TransFlash)	Software	
Maximum memory card size	1 TB	Platform *	Android
Storage media *	Flash	Operating system installed *	Android 14
Graphics		Battery	
Graphics card family	ARM	Battery included	✓
Graphics card	Mali-G57 MC2	Battery technology *	Lithium Polymer (LiPo)
Audio			
Number of built-in speakers	8		

Audio		Battery	
Number of microphones	2	Battery capacity *	8600 mAh
Speakers manufacturer	JBL	Power	
Audio system	Dolby Atmos	AC adapter input voltage	100 - 240 V
Camera		AC adapter frequency	50 - 60 Hz
Rear camera type *	Single camera	Weight & dimensions	
Rear camera resolution (numeric) *	8 MP	Width	268.3 mm
Front camera *	✓	Depth	174.2 mm
Front camera resolution (numeric)	8 MP	Height	13.5 mm
Network		Weight	650 g
Mobile network generation	Not supported	Certificates	
Mobile network connection *	✗	Certification	ErP Lot 26 ErP Lot 6 ENERGY STAR®
Bluetooth	✓		8.0 RoHS compliant TÜV
Bluetooth version	5.2	Operational conditions	
Top Wi-Fi standard *	Wi-Fi 5 (802.11ac)		
Wi-Fi standards	Wi-Fi 5 (802.11ac)	Operating temperature (T-T)	0 - 40 °C
Near Field Communication (NFC)	✗	Operating relative humidity (H-H)	0 - 95%
WWAN	Not installed	Operating altitude	0 - 3048 m
		Other features	
		Warranty period	2 year(s)



0197530284618



197530284618

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 10-MAR-2025. Prints or copies of Information are only valid on the printed Publication date