

Date: **October 11, 2024**

DECLARATION OF CONFORMANCE TO THE EUROPEAN DIRECTIVE EC 1907/2006:
concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)

Dear Customer,

We hereby declare that to the best of our company’s knowledge, our product as listed below is meeting the standards of the European Directive EC 1907/2006 REACH.

None of the substances identified today as Substance of Very High Concern – on the ECHA candidate list of SVHC as valid on **October 11, 2024** (*) – is used in a concentration of more than 0,1 gram/weight.

(*) [Candidate List of substances of very high concern for Authorisation - ECHA \(europa.eu\)](https://europe.ec.europa.eu/en/chemicals-and-hazardous-substances/candidate-list-very-high-concern)

Note: substances imported in the EU by Newell - which require registration - are listed under: **8111110-4/ 8111129-1/ 8111123-3/ 8111124-6/ 8111143-3 /8111148-8/ 8111151-7/ 8111149-1/ 8111150-4/ 8111136-2/ 8111127-5/ 8111128-8** of the company B-Lands, identified as only representative for Newell.

SKU	Material
S0720680	DY D1 9MMX7M BLK/WHT TAPE EU/ANZ
S0720690	DY D1 9MMX7M BLU/WHT TAPE EU/ANZ
S0720710	DY D1 9MMX7M BLK/BLU TAPE EU/ANZ
S0720720	DY D1 9MMX7M BLK/RD TAPE EU/ANZ
S0720730	DY D1 9MMX7M BLK/YLW TAPE EU/ANZ
S0720740	DY D1 9MMX7M BLK/GRN TAPE EU/ANZ
S0720820	DY D1 19MMX7M BLK/CLR TAPE EU/ANZ
S0720870	DY D1 19MMX7M BLK/RD TAPE EU/ANZ
S0720910	DY D1 19MMX7M WHT/BLK TAPE EU/ANZ
S0720500	DY D1 12MMX7M BKL/CLR TAPE EU/ANZ
S0720530	DY D1 12MMX7M BLK/WHT TAPE EU/ANZ
S0720550	DY D1 12MMX7M RD/WHT TAPE EU/ANZ
S0720560	DY D1 12MMX7M BLK/BLU TAPE EU/ANZ
S0720580	DY D1 12MMX7M BLK/YLW TAPE EU/ANZ
S0720590	DY D1 12MMX7M BLK/GRN TAPE EU/ANZ
S0720600	DY D1 12MM WHT/CLR TAPE EU/ANZ
S0720770	DY D1 6MMX7M BLK/CLR TAPE EU/ANZ
S0720780	DY D1 6MMX7M BLK/WHT TAPE EU/ANZ
S0720790	DY D1 6MMX7M BLK/YLW TAPE EU/ANZ
S0720830	DY D1 19MMX7M BLK/WHT TAPE EU/ANZ
S0720860	DY D1 19MMX7M BLK/BLU TAPE EU/ANZ



S0721440	DY LM 240 VOLT ADAPTER EU
S0720980	DY D1 24MMX7M BLK/YLW TAPE EU/ANZ
S0721010	DY D1 24MMX7M WHT/BLK TAPE EU/ANZ
S0722370	DY LW 28X89MM STD ADR LB 260CT EU/AP FSC
S0722410	DY LW 36X89MM CLR ADR LB 260CT EU/AP
S0722430	DY LW 54X101MM SHIP/NB LBL 220CT EU/AP
S0722440	DY LW 54X70MM DISK LBL 320CT EU/AP FSC
S0722470	DY LW 38X190MM LAF LBL 110CT EU/AP
S0722480	DY LW 59X190MM MP LBL 110CT EU/AP
S0720930	DY D1 24MMX7M BLK/WHT TAPE EU/ANZ
S0720970	DY D1 24MMX7M BLK/RD TAPE EU/ANZ
S0720610	DY D1 12MMX7M WHT/BLK TAPE EU/ANZ
S0720880	DY D1 19MMX7M BLK/YLW TAPE EU/ANZ
18445	RHINO 3/4" WHITE VINYL- 19MM
18053	RHINO 3/8" WHITE HEAT SHRINK TUBES- 9MM
S0720570	DY D1 12MMX7M BLK/RED TAPE EU/ANZ
1759398	LI-ION BATT PK R4200/R5200/LM360D/LM420P
520109	DY EMB 3/8"-9MM 10PK BLK TAPE GLOBAL
520106	DY EMB 3.3"-9MM 10PK BLU TAPE GLOBAL
520102	DY EMB 3.3"-9MM 10PK RD TAPE GLOBAL
S0721620	DY LT BLK/YLW TAPE EU
S0721630	DY LT BLK/RD TAPE EU
S0721640	DY LT BLK/GRN TAPE EU
S0721650	DY LT BLK/BLU TAPE EU
S0721730	DY LT BLK/SLV TAPE EU
S0721530	DY LT BLK/CLR TAPE EU
S0718850	DY LT IRON-ON TAPE EU
S0721510	DY LT PAP BLK/WHT TAPE EU (FSC)
2112287	LW DURABLE EU 104MM X 159MM
2112283	LW DRBL RETL EU 25MM X 54MM
2112284	LW DURABLE EU 19MM X 64MM
2112286	LW DURABLE EU 25MM X 25MM
2112285	LW DURABLE EU 25MM X 89MM
2112289	LW DURABLE EU 32MM X 57MM
2112290	LW DURABLE EU 59MM X 102MM
2112288	LW DURABLE EU 59MM X 190MM
S0720890	DY D1 19MMX7M BLK/GRN TAPE EU/ANZ
S0720920	DY D1 24MMX7M BLK/CLR TAPE EU/ANZ
S0722560	DY LW 41X89MM NB LBL 300CT EU/AP FSC
18444	RHINO 1/2" WHITE VINYL- 12MM
S0904980	DY LW 104X159MM SHIP LBL 220CT EU/AP FSC
S0721800	DY LT ASST 3PK TAPE EU (FSC)
S0722400	DY LW 36X89MM LRG ADR LBL 520CT EU/AP
S0722460	DY LW 12X50MM SUSP FILE 220CT EU/AP
S0720090	DY IND METAL TAPE EMBOSSER EU
S0722420	DY LW 54X101MM SHP/NB LBL EU/AP 12PK FSC



S0722390	DY LW 36X89MM LRG ADR LBL EU/AP 24PK FSC
S0722360	DY LW 28X89MM STD ADR LBL EU/AP 24PK FSC
31000	DY EMB ALU NON-ADH 1/2"-12MM TAPE GLOBAL
32500	DY EMB SS NON-ADH 1/2"-12MM TAPE GLOBAL
35800	DY EMB ALU 1/2"-12MM TAPE GLOBAL
S0721660	DY LT PLAST BLK/WHT TAPE EU
S0847750	DY EMB 3.3"-9MM RD/BLU/BLK TAPE EU
S0847730	DY EMB 3.3"-9MM 3PK BLK TAPE EU
1734821	RHINO 1X1" WHITE VINYL SELF LAM
1734523	RHINO 1" WHITE PERM POLY LABEL - 24MM
1734525	RHINO 1" YELLOW FLEX NYLON LABEL - 24MM
1734524	RHINO 1" WHITE FLEX NYLON - 24MM
1805243	RHINO 1/2" BLUE VINYL-12MM
1805417	RHINO 3/4" BLUE VINYL-19MM
1805444	RHINO 1" YELLOW HST-24MM
1805443	RHINO 1" WHITE HST-24MM
1805437	RHINO 3/8" BLACK VINYL-9MM
1805435	RHINO 1/2" BLACK VINYL-12MM
1805436	RHINO 3/4" BLACK VINYL-19MM
1805416	RHINO 1/2" RED VINYL-12MM
1805422	RHINO 3/4" RED VINYL-19MM
1805414	RHINO 1/2" GREEN VINYL-12MM
1805420	RHINO 3/4" GREEN VINYL-19MM
1805430	RHINO 1" WHITE VINYL-24MM
1805431	RHINO 1" YELLOW VINYL-24MM
1805432	RHINO 1" BLACK VINYL-24MM
1805442	RHINO 1/4" WHITE PERM POLY-6MM
18482	RHINO 3/8" WHITE PERM POLY LABEL- 9MM
18485	RHINO 3/8" METAL PERM POLY LABELS- 9MM
18483	RHINO 1/2" WHITE PERM POLY LABEL- 12MM
18486	RHINO 1/2" METALLIZED PERM LABEL- 12MM
622289	RHINO 1/2" CLEAR PERM POLY LABEL-12MM
18484	RHINO 3/4" WHITE PERM POLY LABEL- 19MM
18487	RHINO 3/4" METALLIZED PERM LABEL- 19MM
622290	RHINO 3/4" CLEAR PERM POLY LABEL-19MM
18490	RHINO 1/2" YELLOW FLEX NYLON LABEL- 12MM
18491	RHINO 3/4" YELLOW FLEX NYLON LABEL- 19MM
18488	RHINO 1/2" WHITE FLEX NYLON LABEL- 12MM
18489	RHINO 3/4" WHITE FLEX NYLON LABEL- 19MM
2093096	DYMO D1 BK/WHI 9MMX7M 10 PK
2093097	DYMO D1 BK/WHI 12MMX7M 10 PK
2093098	DYMO D1 BK/WHI 19MMX7M 10 PK
2093091	DYMO LW STD ADDRESS LABELS 28X89MM 12 PK
2093093	DYMO LW LG ADDRESS LABELS 36X89MM 12 PK
2093092	DYMO LW SHIPPING LABELS 54X101MM 6 PK
2093095	DYMO LW MULTIPURPOSE LABEL 32X57MM 12 PK



2093094	DYMO LW MULTIPURPOSE LABELS 32X57MM 6 PK
S0722520	DY LW 25X54MM RE ADR LBL 500CT EU/AP FSC
S0722540	DY LW 32X57MM MP LBL 1000CT EU/AP FSC
S0722530	DY LW 13X25MM MP LBL 1000CT EU/AP FSC
S0722550	DY LW 19X51MM MP LBL 500CT EU/AP FSC
18051	RHINO 1/4" WHITE HEAT SHRINK TUBES- 6MM
18055	RHINO 1/2" WHITE HEAT SHRINK TUBES -12MM
18057	RHINO 3/4" WHITE HEAT SHRINK TUBES- 19MM
18052	RHINO 1/4" YELLOW HEAT SHRINK TUBES- 6MM
18054	RHINO 3/8" YELLOW HEAT SHRINK TUBES- 9MM
18056	RHINO 1/2" YELLOW HEAT SHRINK TUBE- 12MM
18058	RHINO 3/4" YELLOW HEAT SHRINK TUBE- 19MM
18443	RHINO 3/8" WHITE VINYL- 9MM
18508DMO	TAPE CLEAR PERM POLY TAPE 9MM
18435	RHINO 1/2" ORANGE VINYL- 12MM
18432	RHINO 1/2" YELLOW VINYL-12MM
18436	RHINO 3/4" ORANGE VINYL- 19MM
18433	RHINO 3/4" YELLOW VINYL-19MM
S0929100	DY LW 51/89MM APPT/NB LBL 300CT EU/AP
S0929120	DY LW 25X25MM MP LBL 750CT EU/AP FSC
S0947420	DY LW 102X59MM HICAP LRG SHIP LBL EU/AP
1983172	LABELWRITER LARGE ADDRESS 36X89 - 1X260
1983173	LABELWRITER ADDRESS 28X89 / 1X130
1997364	DYMO MICRO USB CABLE
1978366	DY D1 DU 1/2"X10' WHT/RD TAPE GLOBAL
1978367	DY D1 DU 1/2"X10' BLK/ORNG TAPE GLOBAL
1978365	DY D1 DU 1/2"X10' WHT/BLK TAPE GLOBAL
1978364	DY D1 DU 1/2"X18' BLK/WHT TAPE GLOBAL
S0720540	DY D1 12MMX7M BLU/WHT TAPE EU/ANZ
S0720670	DY D1 9MMX7M BLK/CLR TAPE EU/ANZ
S0718040	DY D1 1/2"-12MM NYLON TAPE GLOBAL
S0718050	DY D1 3/4"-19MM NYLON TAPE GLOBAL
S0718060	DY D1 1/2"-12MM PERM POLY TAPE GLOBAL
S0718070	DY D1 3/4"-19MM PERM POLY TAPE GLOBAL
1814308	DYMO LI-POLYMER 7.4 V BATTERY
1868705	DY XTL 0.8X1.6" 21X39MM BK/WT SL TAPE
1868751	DY XTL 0.5" 12MM BK/WT VINYL CONT TAPE
1868752	DY XTL 0.75" 19MM BK/WT VINYL CONT TAPE
1868753	DY XTL 1" 24MM BK/WT VINYL CONT TAPE
1868755	DY XTL 2.0" 54MM BK/WT VINYL CONT TAPE
1868775	DY XTL 2.0" 54MM BK/YL VINYL CONT TAPE
1868809	DY XTL 0.25" 6MM BK/WT HST CONT TAPE
1868810	DY XTL 0.5" 12MM BK/WT HST CONT TAPE
1868811	DY XTL 1" 24MM BK/WT HST CONT TAPE
1888636	DYMO LI-POLYMER 14.8V BATTERY
1888637	DYMO XTL 500 CUTTER MECHANISM



1888662	DYMO XTL 500 AC ADAPTER EU
60622	DY LW PRINT HEAD CLEAN KIT
2025672	DY LW SPOOL
2025676	DY LW POWER CORD EU
2025674	DY LW WIRELESS POWER ADAPTER
2133400	DY LW 54X101MM NAME BDG YLW 220CT EU/AP
2174602	DY EMB JUNIOR GE/UK
2174601	DY EMB OMEGA BLU/GRY DEU/EN
2166659	DY LW 102MM X 210MM DHL LBL 220CT EU
2177563	DY LW 25X54MM RE ADR LB 500CT 12PK FSC
2177564	DY LW 25X54MM RE ADR LB 500CT 6PK EU FSC
2177565	DY LW 102X210MM SHIP LB 140CT 6PK EU FSC
2187329	DY LW 2-3/4"X2-1/8" 70X54MM DOW LBL FSC
2191635	DY LW 54X11MM JWLRY DB2UP1500CT
2191636	DY LW 57MM X 91M ROLL

Signed for and on behalf of: Newell Brands Belgium BV

Place of Issue: Newell Brands Belgium BV

Industriepark-Noord 30

Sint-Niklaas 9100 Belgium

Name: Walker Huang

Function: Product Safety Manager

Signature: Walker Huang

