



Item description

Note:

Additional product features for WAGO Amp Tester:

- AC and DC current measurement
- True RMS measurement
- Data hold function
- Maximum jaw opening: 21 mm Ø
- Compact design for measuring in tight spaces
- Resolution: 0.01 A at 40 A
- Resolution: 0.1 A at 200 A
- Sampling rate: 3 times per second
- Auto power-off function
- CAT III 300 V
- TÜV/GS tested and approved
- IEC/EN 61010-1 (DIN VDE 0411)

Data

Technical Data

Main product function

Test and measurement devices



Material Data

Weight	172 g
--------	-------

Commercial data

Country of origin	CN
GTIN	4050821051206
Customs Tariff No.	90303100900
Product Group	14 (Tools)

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.