



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“Since 1982, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

HYGROCUBE 50

DIGITAL THERMO-HYGROMETER

VERSION 12/21

CE

Nº 10 08 88

Control your atmospheric environment easily and reliably. Just insert batteries, and the temperature and humidity levels are shown on the display. The trend display also gives you an indication as to your specific “comfort climate” and includes heating and ventilation suggestions with clear and easy-to-understand symbols.

HIGHLIGHTS

Clear trend display //

Can be either wall-mounted or used on a table top //

Low battery indicator //

Climate display with time and date value //

Fixed limit values //



GENERAL SPECIFICATIONS

MEASURING RANGE HUMIDITY: 20 % to 90 % **MEASURING RANGE TEMPERATURE:** -9.9 °C to +70 °C **POWER SUPPLY:** 2 x 1.5 V AA battery **WEIGHT:** 120 g **DIMENSIONS (W x H x D):** 80 x 80 x 80 mm (depth for wall mounting: 40 mm)

TECHNICAL DATA

Accuracy of measured relative humidity:	± 6 % (between relative humidity of 30 % - 80 %) ± 8 % (relative humidity of < 30 % and > 80 %)
Accuracy of measured temperature:	± 2.5 % ± 0.9 °C
Storage temperature:	-10 °C to 70 °C
Storage humidity:	10 % to 99 %

PACKAGE CONTENT

Digital Thermo-Hygrometer // 2 x AA battery // Removable wall housing // Installation material (2 dowels + 2 screws) // Operating instructions

This data sheet is published by Voltcraft®, Lindenweg 15, D-92242 Hirschau / Germany, Phone +49 180 586 582 7. The data sheet reflects the current technical specifications at time of print. We reserve the right to change the technical or physical specifications.