

KERN TB200-0.1US.

Kompaktes Arbeitsinstrument für den täglichen Einsatz

KERN[®]



Measuring system

Measuring head diameter:	8 mm
Measuring range [Max]:	20 cm
Precision (of [Max]):	0,005
Readout [d]:	100 µm
Sound velocity (Max):	599,940 mm/min
Test frequency:	5 MHz
Weighing units:	mm

Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

Service

ISO calibration certificate:	961-113
------------------------------	---------

Category

Brand:	Sauter
Category:	Material thickness gauges
Product Group:	Ultrasonic thickness gauge

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	958 g
Net weight:	292 g
Shipping method:	Parcel service

Construction

Cable length:	90 cm
Casing material:	Plastic
Overall dimensions mounted (WxDxH):	161 x 69 x 32 mm