

KERN TE1250-0.1FN.

Ergonomisches Design und externer Messkopf für höchsten Bedienkomfort



Category

Brand:	Sauter
Category:	Coating thickness
Product Group:	Coating thickness gauge

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	750 g
Net weight:	81 g
Shipping method:	Parcel service

Construction

Cable length:	1 m
Casing material:	Plastic
Dimensions housing (WxDxH):	1126 x 65 x 27 mm
Overall dimensions mounted (WxDxH):	131 x 65 x 28 mm

Measuring system

Measuring range [Max]:	100 x 1250 μm
Minimal base thickness:	300 μm
Precision (of [Max]):	3 %
Precision (Offset-Accur):	1 %
Readout [d]:	0 x 0,001 mm
Smallest sample surface, convex (radius):	1,500 mm
Smallest sample surface, flat (radius):	1,500 mm
Smallest sample surface,concave (radius):	2,500 cm
Weighing units:	μm inch (mil)

Display

Display digit height:	1 cm
-----------------------	------

Functions

Calibration tool:	yes
-------------------	-----

Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

Power supply

Operating time:	50 h
-----------------	------

Service

ISO calibration certificate:	961-112
------------------------------	---------