

KERN HBA 100-0.

Handlicher Shore-Durometer mit Schleppzeiger

KERN[®]



Measuring system

Measuring range (Max):	100
Precision (of [Max]):	3 %
Readout:	1
Weighing units:	Shore A

Environmental conditions

Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C

Category

Brand:	Sauter
Category:	Hardness testers

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	180 x 120 x 50 mm
Gross weight:	460 g
Net weight:	150 g
Shipping method:	Parcel service

Construction

Casing material:	metal
Overall dimensions mounted (WxDxH):	115 x 60 x 25 mm