

# KERN FFN15K2IPN



Allround-Tischwaage, geschützt durch Edelstahl und Schutzklasse IP65, auch mit Eichzulassung [M]



## Power supply

Operating time (Backlight off):	50 h
Operating time (Backlight on):	30 h

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

## Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	395 x 308 x 205 mm
Gross weight:	4,600 kg
Net weight:	3,878 kg
Shipping method:	Parcel service
UN number:	2800

## Construction

Dimensions housing (WxDxH):	230 x 300 x 130 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	230 x 300 x 130 mm
Revolving screw feet:	yes
Weighing surface (WxD):	230 x 190 mm

## Measuring system

Adjustment options:	External calibration
Linearity:	4 g
Readout [d]:	2 g
Recommended adjusting weight:	15 kg (M3)
Reproducibility:	2 g
Resolution:	7500
Stabilisation time:	2 s
Tare range:	-15000000 mg
Warm up time:	30 min
Weighing range [Max]:	15 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

## Display

Display digit height:	2,500 cm
-----------------------	----------

## Environmental conditions

Maximum humidity:	95 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C
Minimum humidity:	25 %

## Power supply

Charging time:	12 h
Input voltage:	110 V - 230 V AC
n/a:	CH EURO UK US

n/a:	Mains adapter external
------	------------------------