

KERN FFN6K1IPN



Allround-Tischwaage, geschützt durch Edelstahl und Schutzklasse IP65, auch mit Eichzulassung [M]



Measuring system

| | |
|-------------------------------|----------------------|
| Adjustment options: | External calibration |
| Linearity: | 1 g |
| Readout [d]: | 1 g |
| Recommended adjusting weight: | 6 kg (M3) |
| Reproducibility: | 1 g |
| Resolution: | 6000 |
| Stabilisation time: | 2 s |
| Tare range: | -6000000 mg |
| Warm up time: | 30 min |
| Weighing range [Max]: | 6 kg |
| Weighing system: | Strain gauge |
| Weighing units: | kg lb |

Display

| | |
|-----------------------|----------|
| Display digit height: | 2,500 cm |
|-----------------------|----------|

Environmental conditions

| | |
|--------------------------------|-------|
| Maximum humidity: | 95 % |
| Maximum operating temperature: | 40 °C |
| Minimum ambient temperature: | 0 °C |
| Minimum humidity: | 25 % |

Power supply

| | |
|----------------|------------------|
| Charging time: | 12 h |
| Input voltage: | 110 V - 230 V AC |
| n/a: | CH EURO UK US |

| | |
|------|------------------------|
| n/a: | Mains adapter external |
|------|------------------------|

Power supply

| | |
|---------------------------------|------|
| Operating time (Backlight off): | 50 h |
| Operating time (Backlight on): | 30 h |

Service

Adjustment at the location of installation: 961-248

| | |
|--------------------|---------|
| DAkkS Certificate: | 963-128 |
|--------------------|---------|

Category

| | |
|----------------|-------------|
| Brand: | KERN |
| Category: | Balances |
| Product Group: | Bench scale |

Packaging & shipping

| | |
|-------------------------------|--------------------|
| Delivery: | 24 h |
| Dimensions packaging (WxDxH): | 310 x 400 x 200 mm |
| Gross weight: | 4,680 kg |
| Net weight: | 3,820 kg |
| Shipping method: | Parcel service |
| UN number: | 2800 |

Construction

| | |
|-------------------------------------|--------------------|
| Dimensions housing (WxDxH): | 230 x 300 x 130 mm |
| Level indicator: | yes |
| Material weighing plate: | stainless steel |
| Overall dimensions mounted (WxDxH): | 230 x 300 x 130 mm |
| Revolving screw feet: | yes |
| Weighing surface (WxD): | 230 x 190 mm |