



Discover more details and matching accessories online!

All-round bench scale, protected by stainless steel and IP65 rating, verification optional

Features

- **1** Ideal for the ever-increasing hygienic requirements in the food, pharmaceutical and chemical industries
- Your support in a HACCP-compliant quality system
- **2** Ideal for the robust industrial applications
- **3** Protection against dust and water splashes IP65 (only when using rechargeable battery pack)
- Thanks to rechargeable battery operation, compact, lightweight construction, it is suitable for the use in several locations (kitchens, sales offices, cafeterias, food industry laboratories, etc.)

- Thanks to the stainless steel design of the housing and platform with smooth surface, the scale is rust-free and easy to clean
- Recessed grips on the underside of the scale for easy transportation

Technical data

- Large backlit LCD display, digit height 25 mm
- Dimensions weighing surface, stainless steel, W×D 233×193 mm
- Overall dimensions W×D×H 243×300×127 mm
- Rechargeable battery pack integrated, as standard, operating time up to 50 h without backlight, charging time approx. 12 h
- Net weight approx. 4,0 kg
- Permissible ambient temperature -10 °C/40 °C

STANDARD



3

OPTION



FACTORY



FFN-M

Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Options	
					Verification	Calibr. Certificate
KERN					KERN	DAKKS accr. KERN
FFN 1K-4N	1,5	0,2	-	-	-	963-127
FFN 3K0.5IPN	3	0,5	-	-	-	963-127
FFN 6K1IPN	6	1	-	-	-	963-128
FFN 15K2IPN	15	2	-	-	-	963-128
FFN 25K5IPN	25	5	-	-	-	963-128

Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order.

The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.

FFN 1K-4NM	1,5	0,5	0,5	10	965-227	963-127
FFN 3K1IPM	3	1	1	20	965-227	963-127
FFN 6K2IPM	6	2	2	40	965-228	963-128
FFN 15K5IPM	15	5	5	100	965-228	963-128
FFN 25K10IPM	25	10	10	200	965-228	963-128