

# KERN GAB6K0.05N

Kontroll- und Portionierwaage, auch mit Eichzulassung [M]



## Measuring system

Adjustment options:	External calibration
Linearity:	150 mg
Readout [d]:	50 mg
Recommended adjusting weight:	6 kg (F2)
Reproducibility:	50 mg
Resolution:	120000
Stabilisation time:	2 s
Tare range:	-6000000 mg
Warm up time:	2 h
Weighing range [Max]:	6 kg
Weighing system:	Strain gauge
Weighing units:	g kg

## Display

Display digit height:	2,400 cm
-----------------------	----------

## Counting

Counting resolution:	120000
Minimum piece weight at piece counting (Laboratory):	50 mg
Minimum piece weight at piece counting (Normal):	500 mg

## Functions

Counting function:	yes
Function to save totals:	yes
Percentage determination:	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C

## Power supply

Charging time:	12 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	90 h
Operating time (Backlight on):	40 h
Rechargeable battery:	Rchrg. battery optional - intern

## Service

DAkkS Certificate:	963-128
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	Bench scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	445 x 375 x 205 mm
Gross weight:	4,418 kg
Net weight:	3 kg
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	320 x 330 x 125 mm
Dimensions of display device (WxDxH):	320 x 350 x 125 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	320 x 350 x 125 mm
Revolving screw feet:	yes
Weighing surface (WxD):	294 x 225 mm