

Mini IR Thermometer

Compact thermometer measures up to 630°F (332°C)

With built-in laser pointer that identifies target area and improves aim

Features:

- Backlighting illuminates display for taking measurements at night or in areas with low background light levels
- Automatic Data Hold when trigger released
- Min/Max Hold
- Fixed 0.95 emissivity covers 90% of surface applications
- Auto power off
- Complete with 9V battery and case



Ideal for automotive applications



Test for temperature in heating systems



Check building for insufficient insulation



Convenient carrying case included

Specifications

Range	-4 to 630°F (-20 to 332°C)
Basic Accuracy	±2% of reading +4°F/2°C
Max. Resolution	0.1°F/°C
Emissivity	0.95 fixed
Field of View (Distance to Target)	8:1
Dimensions	3.2 x 1.6 x 6.3" (82x41.5x160mm)
Weight	6.3oz (180g)

Ordering Information:

IR400Mini IR Thermometer (630°F/332°C)
IR400-NISTIR400 with calibration traceable to NIST

