


Rating	300mA
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20°C~+80°C
Color	Red / Black

\*Material:  
 Handle: ABS.  
 Clip: Phosphor bronze.  
 \*Fits O.D. less than  $\phi 2$ mm wire by soldering.



								△
								△
Date	Name	Description					No.	
Drawn	Checked	Approved	SCI BOM No.	Model Name	IC CLIP			
曹盈芳		王作山	Best No.	1085358	Model No.	R8-16F	Rev. X0	
01/08/13		1/8/13	Unit	mm				