

KERN CM150-1N

Die Praktische mit Klappdeckel



Category

Brand:	KERN
Category:	Balances
Product Group:	Pocket balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	205 x 136 x 32 mm
Gross weight:	313 g
Net weight:	165 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	85 x 128 x 25 mm
Material weighing plate:	Plastic
Weighing surface (WxD):	71 x 79 mm

Measuring system

Adjustment options:	External calibration
Linearity:	200 mg
Readout [d]:	100 mg
Recommended adjusting weight:	100 g (M3)
Reproducibility:	100 mg
Resolution:	1500
Stabilisation time:	2 s
Warm up time:	10 min
Weighing range [Max]:	150 g
Weighing system:	Strain gauge
Weighing units:	g tl (Tw) tol

Display

Display digit height:	1,200 cm
-----------------------	----------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Operating time:	70 h
-----------------	------

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate: 963-127