



Discover more details and matching accessories online!

Handy hanging scale for higher loads

Features

- **1** With the TÜV certification mark, the scales meet the requirements of the standard EN 13155 (Non-fixed load lifting attachments/ Breakage resistance) and EN 61010-1 (Electrical safety)
- Ideal for rapid control in goods-in and goods-out
- Also essential in the private sector to determine the weight of fish, game, fruits, bicycle parts, suitcases etc.
- Hold function: For easy reading of the weighing result, the display can be „frozen“ in different ways. Either automatically when the weighing value remains unchanged or manually by pressing the Hold key
- Peak load display (peak hold), Measuring frequency 5 Hz

- [Max] ≤ 200 kg: Snap link (stainless steel) with safety catch and hook (stainless steel) as standard, see larger picture
- **2** [Max] ≥ 500 kg: Reinforced version for heavy loads. Snap link and hook not included, see internet

Technical data

- LCD display, digit height 12 mm
- Hole diameter of load support, model with [Max] ≤ 200 kg: approx. 14 mm [Max] ≥ 500 kg: approx. 16 mm
- Weighing units: kg, lb, N
- Ready for use: Batteries included, 3×1.5 V AA, operating time up to 300 h
- Permissible ambient temperature 5 °C/35 °C

STANDARD



OPTION



| Model       | Weighing capacity | Readability | Dimensions housing<br>W×D×H<br>mm | Net weight<br>approx.<br>kg | Options                                    |
|-------------|-------------------|-------------|-----------------------------------|-----------------------------|--------------------------------------------|
|             |                   |             |                                   |                             | Calibr. Certificate<br>DAkkS accr.<br>KERN |
| KERN        | [Max]<br>kg       | [d]<br>g    |                                   |                             |                                            |
| HCB 20K10   | 20                | 10          | 82×43×153                         | 0,30                        | 963-128H                                   |
| HCB 50K20   | 50                | 20          | 82×43×153                         | 0,30                        | 963-128H                                   |
| HCB 99K50   | 99                | 50          | 82×43×153                         | 0,30                        | 963-129H                                   |
| HCB 50K100  | 50                | 100         | 82×43×153                         | 0,30                        | 963-128H                                   |
| HCB 200K100 | 200               | 100         | 82×43×153                         | 0,30                        | 963-129H                                   |
| HCB 100K200 | 100               | 200         | 82×43×153                         | 0,30                        | 963-129H                                   |
| HCB 200K500 | 200               | 500         | 82×43×153                         | 0,30                        | 963-129H                                   |
| HCB 0.5T-3  | 500               | 1000        | 82×43×153                         | 0,40                        | 963-130H                                   |
| HCB 1T-3    | 1000              | 2000        | 82×48×153                         | 0,60                        | 963-130H                                   |