

Crocodile clips

MA 1 S



Product	MA 1 S
description	Miniature alligator clip with high strength insulation, tin-plated brass/bronze jaws and stainless steel spring. The flat part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinnest wires. Capable of clamping flat components (soldering eyes) and wires up to a maximum diameter of 4 mm.
operating instruction	BA210
article-no. / *colour	9735841xx  00 black  01 red  02 blue  03 yellow  04 green  06 gray  07 white Sn
drawing	
technical data	
connection	2 mm socket
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽²⁾
rated current (consider derating curve)	8 A
material socket	bronze, tin plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-25 °C to +100 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
clamping range	4 mm

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges

⁽²⁾ without rated measurement category, for other circuits that are not directly connected to mains
stand: 21.06.2022

stand: 21.06.2022