

SAUTER FH 5K



Universal digital force gauge for tensile and compressive force measurements with external load cell



Material display housing	plastic
Cable length	3 m
Mounting - force dissipation	Threaded hole M12
Mounting - force application	Threaded hole M12
Load support (tensile force)	Rod end

Functions

Function for averaging	✓
Limit-setting function	✓
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min

Interface

Interfaces	RS-232 standard USB-Device
------------	-------------------------------

Power Supply

Supplied power supply	Accu & Power supply
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	5 V 1000 mA
Power socket for mains adapter	USB C
Battery / accumulator type	NiMH
Battery connection	2-pole tub connector
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	40 h
Rechargeable battery charging time	120 min

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge (external measuring cell)
Product family	FH-M

Measuring System

Measuring range force [Max] (N)	5 kN
Readability force [d] (N)	1 N
Measuring head measuring frequency	2 kHz
Internal data memory: Number of value groups	1
Overload protection (% of [Max])	150%
Tolerance (% of [Max])	0,5%
Internal data memory: Number of individual values	10
Directions of force	tension compression
Default unit	kN

Display

Display type	LCD
Screen reversible	✓

Construction

Dimension housing (W×D×H)	80×55×30 mm
Dimensions completely mounted (W×D×H)	180×55×30 mm
Dimension display device (W×D×H)	240×70×40 mm
Material housing	plastic

SAUTER FH 5K



Universal digital force gauge for tensile and compressive force measurements with external load cell

Services (optional)

Article number for DAkkS calibration (tensile force)	963-163
Article number for DAkkS calibration (compressive force)	963-263
Article number for DAkkS calibration (tensile force/ compressive force)	963-363
Article number for factory calibration (tensile force)	961-163
Article number for factory calibration (compressive force)	961-263
Article number for factory calibration (tensile force/ compressive force)	961-363

Packing & Shipping


Delivery time	1 d
Dimensions packaging (W×D×H)	330×190×175 mm
Shipping method	Parcel service
Net weight approx.	1,4 kg
Gross weight approx.	3,0 kg
Shipping weight	2,82 kg

Product information

GTIN/EAN number	4045761368637
-----------------	---------------

Pictograms

STANDARD



OPTION

