

KERN FK10.

Robustes Zug- und Druckkraftmessgerät für einfache Messungen



DAkkS Calibration certificate (Tensile): 963-1610

DAkkS Calibration certificate (Tensile/Pressure): 963-3610

ISO calibration certificate: 961-361

ISO Calibration certificate (Pressure): 961-2610

ISO Calibration certificate (Tensile): 961-1610

ISO Calibration certificate (Tensile/Pressure): 961-3610

Category

Brand: Sauter

Category: Force gauges

Product Group: Electronic force-measuring device

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 248 x 225 x 80 mm

Gross weight: 872 g

Net weight: 720 g

Shipping method: Parcel service

Construction

Casing material: Plastic

Overall dimensions mounted (WxDxH): 195 x 82 x 35 mm

Measuring system

Measuring range [Max]: 10 N

Overload protection (of [Max]): 200 %

Precision (of [Max]): 0,005

Readout [d]: 0,005 N

Test frequency: 1000 Hz

Display

Display digit height: 1,800 cm

Functions

Data hold function: yes

Display revolving: yes

Peak function: yes

Environmental conditions

Maximum operating temperature: 30 °C

Minimum ambient temperature: 10 °C

Power supply

Input voltage: 100 V - 240 V

n/a: CH EURO UK US

n/a: Mains adapter external

Service

DAkkS Calibration certificate (Pressure): 963-2610