

# KERN EMB5.2K5

Einsteiger-Laborwaage mit enormen Wägeleistungen



## Measuring system

Adjustment options:	External calibration
Linearity:	10 g
Readout [d]:	5 g
Recommended adjusting weight:	5 kg (M1)
Reproducibility:	5 g
Resolution:	1040
Stabilisation time:	2,500 s
Warm up time:	10 min
Weighing range [Max]:	5,200 kg
Weighing system:	Strain gauge
Weighing units:	dwt g oz ozt

## Display

Display digit height:	1,600 cm
-----------------------	----------

## Functions

Suspended weighing:	Hook
---------------------	------

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	0 °C

## Power supply

Charging time:	10 h
----------------	------

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	400 h
Operating time (Backlight off):	50 h
Rechargeable battery:	Rchrg. battery optional

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	School balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	205 x 264 x 67 mm
Gross weight:	705 g
Net weight:	515 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	170 x 240 x 39 mm
Material weighing plate:	Plastic
Weighing surface (d):	150