

# KERN EMB 1200-1

Einsteiger-Laborwaage mit enormen Wägeleistungen



## Measuring system

Adjustment options:	External calibration
Linearity:	300 mg
Readout [d]:	100 mg
Recommended adjusting weight:	1 kg (M1)
Reproducibility:	100 mg
Resolution:	12000
Stabilisation time:	3 s
Warm up time:	30 min
Weighing range [Max]:	1,200 kg
Weighing system:	Strain gauge
Weighing units:	dwt g oz ozt

## Display

Display digit height:	1,600 cm
-----------------------	----------

## Functions

Suspended weighing:	Hook
---------------------	------

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

## Power supply

Charging time:	10 h
----------------	------

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time:	40 h
Operating time (Backlight off):	50 h
Rechargeable battery:	Rchrg. battery optional

## Service

Adjustment at the location of installation: 961-247

DAkkS Certificate:	963-127
--------------------	---------

## Category

Brand:	KERN
Category:	Balances
Product Group:	School balance

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	204 x 267 x 70 mm
Gross weight:	710 g
Net weight:	520 g
Shipping method:	Parcel service

## Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	170 x 240 x 39 mm
Material weighing plate:	Plastic
Weighing surface (d):	150