

KERN EMB5.2K1

Einsteiger-Laborwaage mit enormen Wägeleistungen



n/a: Mains adapter external

Power supply

Operating time: 40 h
Operating time (Backlight off): 50 h
Rechargeable battery: Rchrg. battery optional

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Category

Brand: KERN
Category: Balances
Product Group: School balance

Packaging & shipping

Delivery: 24 h
Dimensions packaging (WxDxH): 205 x 265 x 70 mm
Gross weight: 718 g
Net weight: 472 g
Shipping method: Parcel service

Construction

Casing material: Plastic
Dimensions housing (WxDxH): 170 x 240 x 39 mm
Material weighing plate: Plastic
Weighing surface (d): 150

Measuring system

Adjustment options: External calibration
Linearity: 3 g
Readout [d]: 1 g
Recommended adjusting weight: 5 kg (M1)
Reproducibility: 1 g
Resolution: 5200
Stabilisation time: 3 s
Warm up time: 10 min
Weighing range [Max]: 5,200 kg
Weighing system: Strain gauge
Weighing units: dwt g oz ozt

Display

Display digit height: 1,500 cm

Functions

Suspended weighing: Hook

Environmental conditions

Maximum humidity: 80 %
Maximum operating temperature: 35 °C
Minimum ambient temperature: 5 °C

Power supply

Charging time: 10 h