

KERN CXB30K2

Einsteigermodell ins Profi-Zählen, auch mit Eichzulassung [M], Zählauflösung 30.000 Punkte



Environmental conditions

Maximum humidity:	85 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	15 %

Power supply

Charging time:	8 h
Input voltage:	220 V - 240 V AC 50 Hz
n/a:	EURO
Operating time (Backlight off):	200 h
Operating time (Backlight on):	60 h

Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Category

Brand:	KERN
Category:	Balances
Product Group:	Counting scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	375 x 400 x 178 mm
Gross weight:	5,160 kg
Net weight:	4,200 kg
Shipping method:	Parcel service
UN number:	2800

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	300 x 330 x 110 mm
Level indicator:	yes
Material weighing plate:	stainless steel
Revolving screw feet:	yes
Weighing surface (WxD):	300 x 225 mm

Measuring system

Adjustment options:	External calibration
Linearity:	4 g
Readout [d]:	2 g
Recommended adjusting weight:	20 kg (M1); 10 kg (M1)
Reproducibility:	2 g
Resolution:	15000
Stabilisation time:	2 s
Warm up time:	30 min
Weighing range [Max]:	30 kg
Weighing system:	Strain gauge
Weighing units:	kg

Display

Display digit height: 1,800 cm

Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	1 g
Minimum piece weight at piece counting (Normal):	10 g
Reference weight:	yes

Functions

Counting function:	yes
Function to save totals:	yes