

# KERN IFB15K2DM

Plattformwaage in schwerer Ausführung mit Eichzulassung [M], jetzt auch bis [Max] 600 kg



## Measuring system

Adjustment options:	External calibration
Linearity:	2 g   5 g
Readout [d]:	2 g   5 g
Recommended adjusting weight:	15 kg (M1)
Reproducibility:	2 g   5 g
Resolution:	3 3.000
Stabilisation time:	2 s
Tare range:	-15000000 mg
Warm up time:	10 min   10 min
Weighing range [Max]:	6 kg   15 kg
Weighing system:	Strain gauge
Weighing units:	kg

## Display

Display digit height:	5,200 cm
-----------------------	----------

## Technical data about verification

Minimum load [Min]:	40 g   100 g
Periodic Verification for Italy:	969-112
Verification approval conforming to 2014/31/EU:	yes
Verification by KERN possible:	yes
Verification class:	III
Verification value [e]:	2 g   5 g

## Counting

Counting resolution:	30000
Minimum piece weight at piece counting (Laboratory):	500 mg
Minimum piece weight at piece counting (Normal):	5 g

## Functions

Counting function:	yes
Function to save totals:	yes
Vibration-free weighing (Animal weighing program):	yes
Weighing with tolerance range:	yes

## Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	40 °C
Minimum ambient temperature:	-10 °C
Minimum humidity:	0 %

## Power supply

Charging time:	12 h
Input voltage:	100 V - 240 V 50 / 60 Hz
n/a:	CH EURO UK

n/a:	Mains adapter external
------	------------------------

## Power supply

Operating time (Backlight off):	35 h
Operating time (Backlight on):	8 h
Rechargeable battery:	Rchrg. battery optional (factory)

## Service

Adjustment at the location of installation: 961-248

DAkkS Certificate:	963-128
Verification:	965-228

## Category

Brand:	KERN
Category:	Balances
Product Group:	Industrial scale

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	415 x 700 x 240 mm
Gross weight:	7 kg
Net weight:	6 kg
Shipping method:	Parcel service

## Construction

Cable length of display device:	3 m
Casing material:	Plastic
Dimensions of display device (WxDxH):	250 x 160 x 58 mm

# KERN IFB15K2DM



Plattformwaage in schwerer Ausführung mit Eichzulassung [M], jetzt auch bis [Max] 600 kg

Dimensions of weighing plate (WxDxH):	300 x 240 x 110 mm
of stand:	33 cm
Level indicator:	yes
Material weighing plate:	stainless steel
Overall dimensions mounted (WxDxH):	460 x 240 x 360 mm
Revolving screw feet:	yes
Wall mount:	yes
Weighing surface (WxD):	300 x 240 mm