

KERN FCE6K2N

Einsteiger-Tischwaage à mobil, handlich, leicht



Service

Adjustment at the location of installation: 961-248

DAkkS Certificate: 963-128

Category

Brand: KERN

Category: Balances

Product Group: Bench scale

Packaging & shipping

Delivery: 24 h

Dimensions packaging (WxDxH): 330 x 400 x 190 mm

Gross weight: 2,731 kg

Net weight: 2,188 kg

Shipping method: Parcel service

Construction

Casing material: Plastic

Dimensions housing (WxDxH): 270 x 345 x 106 mm

Dimensions of weighing plate (WxDxH): 252 x 228 x 12,5 mm

Material weighing plate: Plastic

Weighing surface (WxD): 252 x 228 mm

Measuring system

Adjustment options: External calibration

Linearity: 4 g

Readout [d]: 2 g

Recommended adjusting weight: 6 kg (M2)

Reproducibility: 2 g

Resolution: 3000

Stabilisation time: 3 s

Warm up time: 10 min

Weighing range [Max]: 6 kg

Weighing system: Strain gauge

Weighing units: g

Display

Display digit height: 2,500 cm

Environmental conditions

Maximum humidity: 80 %

Maximum operating temperature: 35 °C

Minimum ambient temperature: 5 °C

Power supply

Charging time: 10 h

Input voltage: 220 V - 240 V AC 50 Hz

n/a: CH EURO

n/a: Mains adapter external

Power supply

Operating time: 12 h

Operating time (Backlight off): 20 h

Rechargeable battery: Rchrg. battery optional