



Discover more details and matching accessories online!

Allround parcel scale with robust stainless steel weighing plate – also with XL platform and large weighing ranges

Features

- Weighing plate stainless steel, painted steel base
- Simple and convenient 4-key operation
- Wall mount for display device, standard
- Hold function: When the weighing conditions are unstable, a stable weight is calculated determining an average value
- Protective working cover included with delivery
- Universal external mains adapter included with delivery

Technical data

- Large LCD display, digit height 25 mm
- Weighing platform dimensions, stainless steel
 - A** W×D×H 315×305×57 mm
 - B** W×D×H 550×550×58 mm, see larger picture
 - C** W×D×H 950×500×58 mm
- Dimensions of display device W×D×H 235×114×51 mm
- Optional battery operation, 4×1.5 V AA not included in scope of delivery, operating time up to 60 h
- Permissible ambient temperature 5 °C/35 °C

STANDARD



OPTION



Model	Weighing capacity [Max] kg	Readability [d] g	Reproducibility g	Linearity g	Cable length (Spiral cable) approx. m	Net weight approx. kg	Weighing plate	Options
								Calibr. Certificate DAkkS accr. KERN
KERN								
EOB 15K5	15	5	5	± 10	1,8	3,8	A	963-128
EOB 35K10	35	10	10	± 20	1,8	3,8	A	963-128
EOB 60K20	60	20	20	± 40	1,8	3,8	A	963-129
EOB 60K20L	60	20	20	± 40	2,7	13	B	963-129
EOB 150K50	150	50	50	± 100	1,8	3,8	A	963-129
EOB 150K50L	150	50	50	± 100	2,7	13	B	963-129
EOB 150K50XL	150	50	50	± 100	2,7	17	C	963-129
EOB 300K100A	300	100	100	± 200	1,8	3,8	A	963-129
EOB 300K100L	300	100	100	± 200	2,7	13	B	963-129
EOB 300K100XL	300	100	100	± 200	2,7	17	C	963-129