


Measuring leads

MVL S WS 200/1 Au



Product	MVL S WS 200/1 Au
description	Safety measuring lead, at either end 2 mm diameter safety connector / safety socket with onward connection capability. Gold-plated copper beryllium contact spring. Highly flexible, double insulated stranded lead, shatter-proof grip sleeve and lead. In accordance to IEC 61010 Standard. Built in indicator for easy identification of insulation damages.
operating instruction	BA251
article-no. / *colour	9756987xx  00 black 01 red 02 blue 03 yellow 04 green 05 brown 06 gray 07 white 09 violet 88 yellow green Au
drawing	
	
technical data	
rated voltage	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT III
rated current (consider derating curve)	10 A
material plug	brass, gold plated
housing material	PA
temperature range acc. To IEC61010 ⁽¹⁾	-15 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	V-2
cable length	200 cm
conductor size	1 mm ²
cable material	PVC

2 mm safety system

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges
stand: 21.06.2022

stand: 21.06.2022