



## SOT 23 SURFACE MOUNT BI-COLOR LED LAMP



- 1 CATHODE RED
- 2 CATHODE GREEN
- 3 COMMON ANODE

UNIT : MM[INCH]  
 TOLERANCE : ± 0.25[± 0.01] UNLESS OTHERWISE NOTED

### Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @20mA		Viewing Angle
			Min.	Typ.	2θ 1/2
KM-23ESGW-CA	HIGH EFFICIENCY RED (GaAsP/GaP)	WHITE DIFFUSED	5	10	140°
	SUPER BRIGHT GREEN (GaP)		5	10	

APPROVED: J. Lu	CHECKED: A.Chen	DRAWN : L.N. Sheu	SCALE : 3 : 1	DATA NO. : G1517 DATE : JAN/17/2001	V.1
--------------------	--------------------	----------------------	------------------	--	-----