



Color	:	RGB
Wavelength/color Temperature	:	typ. 620-630Nm, 520-530Nm, 460-480Nm
Length	:	13.5cm
Width	:	1.3cm
Number of LEDs	:	9
Brightness(mcd)	:	300-500, 700-900, 300-500
Viewing angle	:	110°
Voltage	:	max. 12V/DC
Fixing	:	"3M" tape