


L			LM	LH
40	±	1.25	10	27
50	±	1.25	20	27

*The Torx only guarantee the test of go gage

Material: Steel - Grade 4.8

All dimensions in mm

General tolerances:
ISO 4759-1 - C : 1991
ISO 3269 - C
straightness: EN ISO 4759-1:2000 class B
Bild 47 3.2.2.2

Pos.	Quantity	Units	Description	Article no./Drawing no./Standard	Comments
1	2	3	4		6

	Date	Name
Processed	2014.12.20	Chenxu
Checked		
Released		

Scale %

Tolerance see table above

Surface zinc plated 3-5 microns

[redacted]

Hanger connection parts M5

Drawing no. H005-TR

Page 1/1