



First two digits is a spec. code The rest is a lot #

Technical Data	
V max	29.5 V
Q max	65 W
ΔT max	68°
I max	3.9 A
R	5.7 Ohm
Lead wires	20 AWG (0.5mm) ² PVC insulation
Sealing	No Sealing
Solder	Lead Free
Ceramics Al ₂ O ₃ , white 96%	
Maximum processing temperature 200°C	
Tolerances for thermal and electrical parameters ±10 %	
*Close height tolerance ±0.02 -upon request	
T _{hot} =27°C vacuum	

Thermoelectric module
QC -241-1.0-3.9 M

Drawing No ND 014.00.00 C-6