

Speed Sensor (Inductive)

94064 00002



Dimensions		Cam wheel			
Resistance	1050 Ω ± 10 %	Inductivity	1 H	Sealing grade	IP 54 acc. to DIN 40050 (with fitted female connector)
Temperature range	-25 °C to +110°C (130 °C / 1 h)	Mounting hole	M 18 X 1.5	Shaft length	34 ± 0.15 mm
Connector	Connector pin 6.3 x 0.8	Max. working distance	2.0 mm		

Technical status acc. to specification 25.02.1998

General Note This datasheet does not give any information on product availability. The information given is just meant to describe the product and is not to be considered as guaranteed characteristics in the legal sense. All products are subject to design changes in the interest of further technical development.

Copyright: AB Elektronik GmbH (GER) ▪ info@abelektronik.de ▪ www.abelektronik.com