

# Angle sensor (plastic / conductive) 4162400010



<b>Supply</b>	5 ± 0.1 V	<b>Return spring</b>	Yes
<b>Angle range</b>	105°	<b>Voltage range</b>	150 mV – 5,000 mV
<b>Absolute linearity</b>	± 3.0 %	<b>Temperature range</b>	40 °C to + 120 °C
<b>Resistance</b>	4.1 kΩ ± 20 %	<b>Life time full stroke</b>	Min. 2 mio. cycles
<b>Dither life time (± 2°)</b>	Min. 10 mio. cycles	<b>Connector</b>	Female connector on request