

# Temperature sensor

## 94099

NTC sensor



Connector		Dimensions									
		<table border="1" style="margin-left: auto; margin-right: auto;"> <tr> <td>12<sup>-0.15</sup></td> <td>13<sup>+0.1</sup><sub>-0.1</sub></td> </tr> <tr> <td>19<sup>-0.15</sup></td> <td>20<sup>+0.2</sup><sub>-0.1</sub></td> </tr> <tr> <td>15<sup>-0.15</sup></td> <td>16<sup>+0.15</sup><sub>-0.1</sub></td> </tr> <tr> <td>Ø d</td> <td>Ø D</td> </tr> </table>		12 <sup>-0.15</sup>	13 <sup>+0.1</sup> <sub>-0.1</sub>	19 <sup>-0.15</sup>	20 <sup>+0.2</sup> <sub>-0.1</sub>	15 <sup>-0.15</sup>	16 <sup>+0.15</sup> <sub>-0.1</sub>	Ø d	Ø D
12 <sup>-0.15</sup>	13 <sup>+0.1</sup> <sub>-0.1</sub>										
19 <sup>-0.15</sup>	20 <sup>+0.2</sup> <sub>-0.1</sub>										
15 <sup>-0.15</sup>	16 <sup>+0.15</sup> <sub>-0.1</sub>										
Ø d	Ø D										
<b>Media</b>	Liquid media e.g. water, oil	<b>Connector</b>	AMP Junior Power Timer, 2-pole								
<b>Nominal resistance</b>	2,251 Ω (25 °C) 153 Ω (100 °C) *	<b>Protection range</b>	IP 69								
<b>Temperature range</b>	- 40 °C to + 150 °C	<b>Order number</b>	Diameter 12 mm 9409900012								
<b>Time of response</b>	T90 ≤ 15 s (water)	<b>Order number</b>	Diameter 15 mm 9409900015								
<b>Hose diameter</b>	12 mm, 15 mm, 19 mm	<b>Order number</b>	Diameter 19 mm 9409900019								