



Technical Data	
V max	3.9 V
Q max	2.6 W
ΔT max	72°
I max	1.2 A
R	2.77 Ohm
Lead wires	Cu wire Sn plating
Sealing	No sealing
Solder	Lead Free
Ceramics	Al ₂ O ₃ , white 96%
Maximum processing temperature	+170°C
Tolerances for thermal and electrical parameters $\pm 10\%$	

Thermoelectric module

Drawing No ND 076.00 C-14

QC-32-0.6-1.2

Certified ISO 9001:2000