





SPECIFICATION

Current Rate:1 AMP
 Insulation Resistance:5000M Ω Min
 Contact Resistance:20m Ω Max
 Dielectric voltage:1000V AC for one minute
 Operation Temperature:-55°C to +150°C
 Soldering Temperature:200°C / 5~10 Sec

MATERIAL

Insulator:UL 94V-0
 Contact Pin:Phorphos Bronze

ORDER INFORMATION



A, B, C, D Tolerance is ±0.2

No. of conatctcs	6-B	8-B	14-B	16-B	18-B	20-B	22-B	24-A	28-A	32-A	24-A 24-B	28-A 28-B	32-A 32-B	40-A 40-B	42-A	48-B
A	7.62	10.16	17.78	20.32	22.86	25.40	27.94	30.48	35.56	40.64	30.48	35.56	40.64	50.80	53.34	60.96
B	5.08	7.62	15.24	17.78	20.32	22.86	25.40	27.94	33.02	38.10	27.94	33.02	38.10	48.26	50.80	58.42
C	10.00										17.50					
D	7.62										15.24					
	IC1-3XX										IC1-6XX					

AREA	REV.	DESCRIPTION	DATE

品名 TITLE	STAMPED PIN IC SOCKET CONNECTOR PITCH 2.54mm				
	品號 PART NO.	IC1-XXX-L		日期 DATE	12/21/2007
	圖號 DRAWING NO.	IC1-XXX-L	版本 REV.	A	繪圖 DRAWN
	客戶品號 CUSTOMER P/N		比例 SCALE	FREE	核對 CHECKED
	公差 TOLERANCE	.X ±0.3 .XX ±0.25	單位 UNIT	mm	核准 APPROVED