


### SPECIFICATION

Current Rate:3 AMP  
 Insulation Resistance: $\geq 1000M\Omega$  at  $V=100V$ .  
 Contact Resistance: $\leq 4m\Omega$ /Contact  
 Dielectric voltage:1000V AC for one minute  
 Operation Temperature: $-40^{\circ}C$  to  $+105^{\circ}C$




### MATERIAL

Insulator:PBT(UL94V-0)  
 Contact Pin:Copper Alloy

### ORDER INFORMATION



No. of Contacts	Dim. A	Dim. B	Type
06	7.62	5.08	W/O Central Support
08	10.16	7.62	
10	12.70	10.16	
14	17.78	15.24	
16	20.32	17.78	Wlth Central Support
18	22.86	20.32	
20	25.40	22.86	
24	30.48	27.94	
28	35.56	33.02	
32	40.64	38.10	
40	50.80	48.26	
48	60.96	58.42	



P.C.B LAYOUT

品名 TITLE	MACHINE PIN SOCKET IC STRAIGHT TYPE 2.54mm				
品號 PART NO.	MSIC-3XX-L			日期 DATE	2009/11/18
圖號 DRAWING NO.	MSIC-3XX-L	版本 REV.	A	繪圖 DRAWN	Sinnys
客戶品號 CUSTOMER P/N		比例 SCALE	FREE	核對 CHECKED	Paul
公差 TOLERANCE	.X $\pm 0.30$ .XX $\pm 0.20$	單位 UNIT	mm	核准 APPROVED	James

AREA	REV.	DESCRIPTION	DATE