


### SPECIFICATION

Current Rate:1 AMP  
 Insulation Resistance:1000M Ω Min  
 Contact Resistance:30m Ω Max  
 Dielectric voltage:600V AC for one minute  
 Operation Temperature:-50°C to +105°C  
 Soldering Temperature:200°C / 5 Sec

### MATERIAL


Insulator:Hi-temp PBT. UL 94V-0  
 Contact material:Phorphos Bronze Jis 5210  
 contact Platred:150U" tin over 40U" nickel






Recommended PCB Layout  
 (PCB TOLERANCE ±0.05)

| No. of contact | A±0.15 | B±0.15 | C±0.1 | D±0.1 | E±0.1 | F±0.1 |
|----------------|--------|--------|-------|-------|-------|-------|
| 20             | 15.50  | 15.50  | 5.08  | 5.08  | 5.08  | 5.08  |
| 28             | 18.04  | 18.04  | 7.62  | 7.62  | 7.62  | 7.62  |
| 32             | 18.04  | 20.60  | 7.62  | 10.16 | 7.62  | 10.16 |
| 44             | 23.48  | 23.48  | 12.70 | 12.70 | 12.70 | 12.70 |
| 52             | 25.88  | 25.88  | 15.24 | 15.24 | 15.24 | 15.24 |
| 68             | 31.66  | 31.66  | 20.32 | 20.32 | 20.32 | 20.32 |
| 84             | 36.66  | 36.66  | 25.40 | 25.40 | 25.40 | 25.40 |

### ORDER INFORMATION



©:Standard Recommend



|                      |                               |             |      |                |            |
|----------------------|-------------------------------|-------------|------|----------------|------------|
| 品名<br>TITLE          | PLCC SOCKET THROUGH HOLE TYPE |             |      |                |            |
| 品號<br>PART NO.       | DPLCC-XX-L                    |             |      | 日期<br>DATE     | 08/08/2005 |
| 圖號<br>DRAWING NO.    | DPLCC-XX-L                    | 版本<br>REV.  | B    | 繪圖<br>DRAWN    | Kent       |
| 客戶品號<br>CUSTOMER P/N |                               | 比例<br>SCALE | FREE | 核對<br>CHECKED  | Paul       |
| 公差<br>TOLERANCE      | .X ±0.3<br>.XX ±0.25          | 單位<br>UNIT  | mm   | 核准<br>APPROVED | James      |

| AREA | REV. | DESCRIPTION | DATE |
|------|------|-------------|------|
|      |      |             |      |