

**SPECIFICATION**

Current Rate:1 AMP  
 Insulation Resistance:1000M Ω Min  
 Contact Resistance:30M Ω Max  
 Dielectric voltage:600V AC for one minute  
 Operation Temperature:-50°C to +105°C  
**MATERIAL**  
 Insulator:Hi-temp PPS, UL 94V-0  
 Contact material:Phorphos Bronze Jis 5210  
 contact Plated:150U" tin over 40U" nickel

**ORDER INFORMATION**

SPLCC- XX I N  
 1 2 3

© 1.No. of contacts  
 (20,28,32,44,52,68,84)

© 2.G:Gold flash

T: Tin plated

S: Selective

A: 50"

B: 10U"



C: 20U"

D: 30U"

E: Tin 200U"

© 3.N:PPS/Brown

B: PPS/Black



P.C.B LAYOUT

NO OF CONTACT	A±0.2	B±0.2	C±0.1	D±0.1	E±0.2
20	15.66	15.66	5.08	5.08	17.28
28	18.20	18.20	7.62	7.62	20.87
32	18.20	20.74	7.62	10.16	22.60
44	23.28	23.28	12.70	12.70	28.30
52	25.82	25.82	15.24	15.24	31.65
68	30.90	30.90	20.32	20.32	38.83
84	35.98	35.98	25.40	25.40	46.00

AREA	REV.	DESCRIPTION	DATE

品名 TITLE	PLCC SOCKET SURFACE MOUNT TYPE					
品號 PART NO.	SPLCC-XX				日期 DATE	08/20/2002
圖號 DRAWING NO.	SPLCC-XX	版本 REV.	A	繪圖 DRAWN	Kent	
客戶品號 CUSTOMER P/N		比例 SCALE	FREE	核對 CHECKED	Paul	
公差 TOLERANCE	.X ±0.2 .XX ±0.1	單位 UNIT	mm	核准 APPROVED	James	