

**Cable markers
LM WRITE ON 25X68 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



LM WriteOn cable markers on DIN A4 sheets are used for labelling conductors and cables up to an outside diameter of 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Easy and quick labelling with a DIN A4 laser printer or STI pen

General ordering data

Type	LM WRITE ON 25X68 WS
Order No.	1695731044
Version	Cable markers, Label, 68 x 25 mm, Polyester film, Colour: White
GTIN (EAN)	4008190924706
Qty.	10 pc(s).

Cable markers LM WRITE ON 25X68 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	68 mm	Width	25 mm
Depth	0.2 mm	Net weight	10 g

General data

Adhesive	Acrylate	Colour	White
Material	Polyester film	Material colour according to resistance code	9
Number per sheet	28	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Size of labelling field	25 x 17 mm
Type of printing	blank	UL 94 flammability rating	HB

Conductor and cable markers

Conductor O.D., max.	14.3 mm	Conductor O.D., min.	8.2 mm
Conductor cross-section, max.	70 mm ²	Conductor cross-section, min.	16 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	lab_lm_write_on_25x68_mcf.zip
---------------------------------	---