


Accessories SKMU PG11-K GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

General ordering data

Type	SKMU PG11-K GR
Order No.	1697460000
Version	Accessories, Locknut, Polyamid 6 (PA6 - GF30), PG 11
GTIN (EAN)	4008190880576
Qty.	100 pc(s).

Accessories SKMU PG11-K GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	1.2 g
------------	-------

Width

Thickness	5 mm
-----------	------

General information

AF size 1	24 mm	Cable gland	PG
Colour code	RAL 7035	External thread	PG 11
Internal thread	PG 11	Length of thread	5 mm
Material	Polyamid 6 (PA6 - GF30)	O.D.	27.72 mm
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Thickness	5 mm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000940	UNSPSC	30-21-18-01
eClass 5.1	23-11-07-01	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Further versions on request
--------------------------------	-----------------------------

Approvals

Approvals



ROHS	Conform
------	---------