

**Clamping yoke
BS 35II KLBUE3-8**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals.

These are available in different versions.

General ordering data

Type	BS 35II KLBUE3-8
Order No.	1723810000
Version	Clamping yoke, Set of fixings, Steel, 35 mm
GTIN (EAN)	4008190377007
Qty.	10 pc(s).

Clamping yoke BS 35II KLBUE3-8

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	35 mm	Net weight	56.538 g
Diameter	3 mm		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Rated data IECEx/ATEX

Marking EN 60079-7	Ex e II
--------------------	---------

Additional technical data

Explosion-tested version	No	Version	Clamping bracket
--------------------------	----	---------	------------------

Material data

Material	Steel	Colour	Silver
----------	-------	--------	--------

System specifications

Product family	Clamping yoke
----------------	---------------

Classifications

ETIM 3.0	EC001741	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-18-92-34		

Approvals

Approvals	
ROHS	Conform