






Audio Analyzer

K8098



Small and compact unit
Ideal for panel mounting
Give your home made audio gear a high-tech look
Upgrade existing equipment
Applications: Amplifiers, pre-amps, mixing panels, MP3 players, PC, in-car use etc...

Features:

Measure

- Peak power
- RMS power
- Mean dB
- Peak dB
- Linear audio spectrum
- Third Octave audio spectrum

Auto or manual range selection


Peak -hold function

Speaker impedance selection

Language selection

White backlit LCD

Easy panel mounting



Technical:

Power measurement into 2, 4 or 8 ohm

Range: 300mW to 1200W@20hm

Sensitivity: -34dBu (15.5 mVrms)

Max input level: 50Vrms @ 220k

Freq. Range: 20Hz to 20kHz

Power supply: 12VDC / 75mA

Display: 128x64 (46x24mm)

Dimensions:

Front panel: 98x51mm (3.8" x 2")

Mounting depth: 35mm (1.37")

Upcoming module version VPA20