





**4-Channel digital input module DC 24  
V positive switching 3-wire connection  
750-1420**

|  |               |
|--|---------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                             | 750-1420      |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b> | 0.08 - 2.5    |
| <b>Cross section2 (Cross section / AWG)</b>            | 28 - 14       |
| <b>Strip length (Strip length / mm)</b>                | 8 - 9         |
| <b>Height (Height / mm)</b>                            | 64            |
| <b>Width (Width / mm)</b>                              | 12            |
| <b>Depth (Depth / mm)</b>                              | 100           |
| <b>COLOR (COLOR)</b>                                   | lichtgrau     |
| <b>Comment (Comment)</b>                               | 24V DC 3,0 ms |