





**CANopen Fieldbus Coupler D-Sub 10  
kBaud - 1 MBaud DIGITAL AND  
ANALOG SIGNALS  
750-338**

<b>ITEM-NO. (ITEM-NO.)</b>	750-338
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 14
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Height (Height / mm)</b>	65
<b>Width (Width / mm)</b>	51
<b>Depth (Depth / mm)</b>	100
<b>COLOR (COLOR)</b>	lichtgrau