





2-CHANNEL DIGITAL INPUT MODULE
DC 48 V 3,0 ms
750-412

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

| | |
|--|---------------|
| ITEM-NO. (ITEM-NO.) | 750-412 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 14 |
| Strip length (Strip length / mm) | 8 - 9 |
| Height (Height / mm) | 64 |
| Width (Width / mm) | 12 |
| Depth (Depth / mm) | 100 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | 46.5 |
| Comment (Comment) | 48V DC 3.0 ms |