





**1-CHANNEL INPUT MODULE FOR
RESISTANCE JUMPERS (DMS) for DIN
35 rail
750-491**

| | |
|--|-----------------|
| ITEM-NO. (ITEM-NO.) | 750-491/000-001 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 14 |
| Strip length (Strip length / mm) | 8 - 9 |
| Height (Height / mm) | 64 |
| Width (Width / mm) | 12 |
| Depth (Depth / mm) | 100 |
| COLOR (COLOR) | lichtgrau |
| WEIGHT (WEIGHT / g) | 53 |
| Comment (Comment) | DMS / 65 ms |